



Optimal separation

The Vibro® Technology enables you to achieve higher transmissions and a superior separation. This is due to the 100% uniform Trans Membrane Pressure (TMP), securing an optimal membrane performance.

Perfect for food and pharmaceutical production

All engineering solutions are sanitary and all parts in media contact are in FDA and EC 1935/2004 compliant materials, and can be made for GMP use.

Energy consumption reduced by up to 95 %

The Vibro® Technology makes the cross flow pump redundant, thereby minimizing the energy requirements for pumping and cooling.



Vibro-I

Product Sheet

Vibro-I 2.5 m² / 5 m²

Option: barb connections

Weight	55 / 74 kg (full)
Dimensions (L x W x H)	665 / 905 mm x 400 mm x 650 mm
Membrane	1 / 2 x 2.5 m ² Free Flow Plate Modules (HP1)
Internal Retentate Volume	5.5 / 9.5 l, Fully Drainable
Internal Permeate Volume	0.7 / 1.4 l, Fully Drainable
Operating Pressure	0 - 4 bar at 5 - 35°C, 0 - 3 bar at 5 - 55°C and 0 - 1 bar at up to 80°C
Vibration Motor	400 VAC, 50 Hz, 480 W

Vibro-I 10 m²

Option: on wheels

Weight	130 kg (full)
Dimensions (L x W x H)	625 mm x 504 mm x 1230 mm
Membrane	4 x 2.5 m ² Free Flow Plate Modules (HP1)
Internal Retentate Volume	17.5 l, Fully Drainable
Internal Permeate Volume	2.8 l, Fully Drainable
Operating Pressure	0 - 4 bar at 5 - 35°C, 0 - 3 bar at 5 - 55°C and 0 - 1 bar at up to 80°C
Vibration Motor	400 VAC, 50 Hz, 480 W

Vibro-I 20 m²

Weight	180 kg (full)
Dimensions (L x W x H)	650 mm x 600 mm x 2420 mm
Membrane	8 x 2.5 m ² Free Flow Plate Modules (HP1)
Internal Retentate Volume	33.5 l, Fully Drainable
Internal Permeate Volume	5.6 l, Fully Drainable
Operating Pressure	0 - 4 bar at 5 - 35°C, 0 - 3 bar at 5-55°C and 0-1 bar at up to 80°C
Vibration Motor	400VAC, 50Hz, 900 W

Vibro-I 40 m²

Weight	480 / 565 kg (drained / full)
Dimensions (L x W x H)	1000 mm x 860 mm x 1610 mm
Membrane	16 x 2.5 m ² Free Flow Plate Modules (HP1)
Internal Retentate Volume	70 l, Fully Drainable
Internal Permeate Volume	11.2 l, Fully Drainable
Operating Pressure	0-4 bar at 5-35°C, 0-3 bar at 5-55°C and 0-1 bar at up to 80°C
Vibration Motor	400VAC, 50Hz, 3,200 W

Vibro-I 80 m²

Weight	660 / 815 kg (drained / full)
Dimensions (L x W x H)	1000 mm x 860 mm x 2660 mm
Membrane	32 x 2.5 m ² Free Flow Plate Modules (HP1)
Internal Retentate volume	134 l, Fully Drainable
Internal Permeate Volume	22.4 l, Fully Drainable
Operation Pressure	0-4 bar at 5-35°C, 0-3 bar at 5-55°C and 0-1 bar at up to 80°C
Vibration Motor	400VAC, 50Hz, 3,200 W

Vibro-I Media In/Out

Retentate Standard	1 x DN25 Tri-Clamps (top & bottom) and 1 x 1/2" thread (top)
Retentate Options	Combinations of 1/4", 1/2" 3/4" threads and Tri-Clamps
Permeate Standard	1/4" to 10 mm Push-In Tee Fitting
Permeate Options	1/4" to miniclamp
More options are available upon request	

HP1 Module Membranes

Membrane type	Cut-off	Membrane Material
UF	1 - 800 kDa	PES, PESH, PVDF, PAN, RC
MF	800 kDa - 1 µm	PVDF, PTFE



SANI 
Membranes

SANI Membranes A/S
Ryttermarken 8 | DK-3520 Farum
Denmark
www.sanimembranes.com